



DATA SHEET



LAB COAT WITH BOTTONS, WITHOUT POCKETS. PE.







WHITE **BLUE**



TYPE



VIRGIN POLYPROPYLENE 100% Gauge 70



SINGLE SIZE



COMPLIES

WITH FOOD

REGULATION

2011/10/CE

LINE OF **PRODUCT**

IDD uniuso

ח	FS	CR	IPTI	ON
_		~,		

REFERENCE	ТҮРЕ	PACKING	DIMENSIONS	CARTON WEIGHT	N° CARTONS BY PALLET
05/01/010	WHITE WITH HOOKS	1 pc/bag 100 pcs/carton	41 x 21 x 21 cm	3,78 Kg	50 boxes
05/01/011	BLUE WITH HOOKS	1 pc/bag 100 pcs/carton	41 x 21 x 21 cm	3,78 Kg	50 boxes

PACKING (Complies with UE Normative 2016/425)

BOX MATERIAL: Recycled cardboard



Carton printing:

- Reference
- Batch number
- Descriptions in spanish, english, french, italian and portuguese
- Units
- EAN code
- CE mark
- Pictograms for handling and product preservation.

SAMPLE VIEW

WEIGHT: 2,57gr*. Bag printing:



SAMPLE VIEW

Single bag without

print: 100% virgin polyethylene (0%

recycled)

- Units - EAN code

- CE mark

- Reference

- Recycling pictogram

BAG MATERIAL: 100% virgin polyethylene (0% recycled)

*Weight is a statistic and is subject to variation.

- Descriptions in spanish, english,

french, italian and portuguese

QUALITY CONTROL



QUALITY CONTROL IN ORIGIN QUALITY CONTROL AT DESTINATION

PRODUCTION



- CUTING
- SEWING
- QUALITY CONTROL
- PACKING

USE

It is recommended to use the product only once time, longer use or more than one use will minimize the functions which it has been manufactured for. For wearing, you should be careful not to strecht it more than the product allows as there is a risk of breaking the tissue.

STORAGE

Keep it in its original packaging and in dry areas at temperatures between 10°C and 30°C. Do not expose to direct sunlight.

OTHER FABRICS

Polyethylene hooks.


OTHER KEY POINTS

Odorless, breathable, hypoallergenic.

Distributed by:







SIZES						
POINT TO CHECK	SIZE (CM)	TOLERANCE (CM)	HOW TO CHECK			
Α	120	(+/-2,0)	PLANE			
В	70	(+/-1,0)	PLANE			
С	80	(+/-2,0)	PLANE			
D	140	(+/-2,0)	CLOSED CONTOUR			
E	25	(+/-1,0)	STRAIGHT FIST			
F	25	(+/-1,0)	PLANE			
G	28	(+/-1,0)	PLANE			
Н	1	(+/-0,0)	DIAMETER			
I	20	(+/-2,0)	PLANE			